






1 INSTRUCTIONS AND RECOMMENDATIONS



Switch off the mains before commencing any work




Same connection for a Dual USB DATA mechanism ref 087-460



For single units, use casings 50mm deep, diameter 67 or 68mm


2 WIRING

Connect the male plug to the mechanism



3 FITTING

After wiring according to the instructions, place the mechanism in the flush-mount box and screw on the plate according to the diagram opposite.




Screws supplied with the flush-mount box.

4 TABLE OF RELEVANT REFERENCES


Reference and description:

Compatible with:




087-450G S USB DATA
087-460G D USB DATA

Confidence and Fascination
Collection



087-450B S USB DATA
087-460B D USB DATA

Désir, Karo and Hitera
Collection



087-450W S USB DATA
087-460W D USB DATA

Iris Collection

5 CERTIFICATIONS

USB DATA 2.0

